



SNAPSHOT MOSAIC HYPERSPPECTRAL IMAGING CAMERA

Imec's snapshot mosaic hyperspectral imaging technology offers seamless integration of spectral imaging when integrated in to compact and robus standard GigE machine vision camera like the PhotonFocus MV1-D2048x1088-HS01-96-G2 series.

READY-TO-USE HYPERSPPECTRAL CAMERA FOR MEDICAL & INDUSTRIAL APPLICATIONS

HYPERSPPECTRAL TECHNOLOGY FOR REAL-WORLD APPLICATIONS

Hyperspectral cameras, compared to traditional cameras, divide the light spectrum in many small wavelength bands. Therefore, a hyperspectral camera captures the spectral fingerprint of any object, a unique spectral curve signature giving very detailed information about its exact constitution.

imec's hyperspectral filters processing capabilities enables snapshot acquisition and reconstruction and classification of HSI datacubes at video rates.


HYPERSPPECTRAL EVALUATION SYSTEM

Our hyperspectral evaluation systems enable efficient evaluation and use of imec's unique hyperspectral imagers. Although linescan system needs a translational movement to capture the different hyperspectral bands of an object, no scanning movement is needed with our snapshot design to capture the hyperspectral datacubes.

The OEM camera consists of the following elements:

- imec snapshot mosaic hyperspectral image sensor
- PhotonFocus GiGeVision camera
- Custom band-pass rejection filter on glass with 25mm mount
- Lens
- Cable interface

IMEC HYPERSPECTRAL IMAGER & CAMERA HARDWARE SPECIFICATIONS



Packaged hyperspectral snapshot mosaic, 16 and 25 bands, hyperspectral image sensor from imec

Acquisition mode	snapshot mosaic
Number of spectral bands	16 bands in 460-620 nm range (SNm4x4 VIS version) 16 bands in 595 – 860 nm range (SNm4x4 RedNIR version) 25 bands in 665 – 975 nm range (SNm5x5 NIR version)
Bandwidth per band (FWHM)	< 15nm, collimated
Imager type	CMOS imager, CMOSIS CMV2000
Imager size	2.2Mpixels
Spatial resolution (RAW)	512 x 272 RAW per band (SNm4x4 VIS version) 512 x 272 RAW per band (SNm4x4 RedNIR version) 409 x 218 RAW per band (SNm5x5 NIR version)
Frame rate	Up to 42 fps hyperspectral cubes/second at full resolution
Interface	GiGeVision & triggering
Pixel pitch	5.5µm
Bit depth	8 or 10bit
Optical input	(near) telecentric
Dimensions	50x50x50mm
Weight	120g without fore-optics

POTENTIAL APPLICATIONS

- Optical sorting in machine vision
- Chemical analysis of material composition
- Food safety & inspection
- Medical & healthcare
- Pharmaceutical manufacturing
- Semiconductor & photovoltaic
- Security & surveillance
- Waste recycling
- Human-machine interface
- Mineralogy, mining
- And more ...

JEROME BARON

jerome.baron@imec.be
+32 16 28 32 82

DISCLAIMER - This information is provided 'AS IS', without any representation or warranty. Imec is a registered trademark for the activities of IMEC International (a legal entity set up under Belgian law as a "stichting van openbaar nut"), imec Belgium (IMEC vzw supported by the Flemish Government), imec the Netherlands (Stichting IMEC Nederland, part of Holst Centre which is supported by the Dutch Government), imec Taiwan (IMEC Taiwan Co.) and imec China (IMEC Microelectronics (Shanghai) Co. Ltd.) and imec India (Imec India Private Limited), imec Florida (IMEC USA nanoelectronics design center).